



TECHNICAL DATA SHEET

FLEXI-TECH 60 F.G.

Two Component Solvent Free Polyurethane Elastomer



Thortex Flexi-Tech 60 F.G. is a 60 Durometer high performance fluid elastomer which has been specifically developed for the resurfacing of rubber components and is suitable for use on impellers, chutes, hoppers, valves, rollers, gaskets, hoses, conveyor belts, off road tyres etc.

The **Thortex Flexi-Tech 60 F.G.** formulation is based on a complex blend of polyols and polyesters in combination with amine catalysts and activators to produce a cold vulcanising product with outstanding mechanical strength.

The properties of **Thortex Flexi-Tech 60 F.G.** have been designed to match factory produced rubbers.

Before proceeding, please read the following information carefully to ensure that the correct application procedure is fully understood.

SURFACE PREPARATION

All existing dirt, oil and grease should be removed and the surface wiped with **Thortex Universal Cleaner**.

Any areas of frayed or fragmented rubber should be cut away to provide a sound repair area.

Smooth surfaces, including metals, should be mechanically etched to produce a good profile, with abrasive blasting being preferred for metal substrates. Rubber surfaces are best roughened using a stiff wire brush / comb.

Edges of repair areas of belts, hoses, tyres etc. should be undercut.

All loose dust and particles should be blown clear of the prepared surface.

On certain repairs such as gaskets and castings where one surface is not required to bond to the **Thortex Flexi-Tech 60 F.G.**, these surfaces should be treated with **Thortex Release Agent**.

PRIMING

All areas to be repaired or resurfaced should be first primed with **Thortex Flexi-Tech Primer**.

The primer should be applied with a soft bristled brush to give an even, but low coating thickness, taking care to avoid ponding of the primer.

The primer should be allowed a minimum of 60 minutes and a maximum of 8 hours at 20°C (68°F) before applying the **Thortex Flexi-Tech 60 F.G.**

Where a faster drying primer is required **Thortex Flexi-Tech 60 R.G. Primer** can be used. Please refer to **Thortex Flexi-Tech 60 R.G.** Tech Sheet.

MIXING

Thortex Flexi-Tech 60 F.G. is a two component material which must be mixed together prior to use.

The contents of the base container should be transferred to the mixing container provided. The contents of the activator should be added to the base with continuous stirring to produce a streak free viscous liquid.

Where less than full unit mixes are required it is essential that the product be mixed accurately weighing out the quantities of base and activator.

Thorough mixing is extremely important, and once the material appears mixed, a further period of mixing should be carried out to ensure there is no unmixed material.

The mixed material should be used within 30 minutes of mixing at 20°C (68°F).

APPLICATION

For resurfacing the mixed material should be applied evenly to the primed surface with a clean brush. When a second coat is required this should be applied as soon as possible, after the initial set and within 24 hours of the first coat being applied.

For casting / moulding the mixed product should be poured into the prepared mould, the filled mould should be gently vibrated to aid the release of trapped air.

All equipment must be cleaned IMMEDIATELY after use with **Thortex Universal Cleaner**.

Volume Capacity

900cc (54.8 cu ins) per kilo

Detailed working recommendations are available from the Technical Centre on request.

PHYSICAL CONSTANTS

Mixing Ratio	Base	Activator	
	2	1	By volume
	2	1	By weight

Appearance	Base	Activator
	Opaque Soft Gel	Coloured Viscous Liquid

Drying & Cure times at

20°C (68°F)	Usable Life	25 minutes
	Initial Set	3 hours
	Machining	16 hours
	Full Mechanical	3 days

Volume Solids 100%

V.O.C. Nil

Shelf Life Use within 12 months of purchase. Store in original sealed containers at temperatures between 5°C (40°F) and 30°C (86°F).

FOR FURTHER INFORMATION PLEASE CONTACT

PHYSICAL PROPERTIES

Tensile Strength ASTM D412	70 kg/cm ² (1000 psi)
Tear Strength ASTM D624	36 kg/cm (200 pli)
Elongation ASTM D412	800%
Shore A Hardness ASTM D2240	60
Peel Adhesion (concrete and steel) ASTM D903	9 kg/cm (50 pli) - cohesive failure in Flexi-Tech
Dielectric Strength ASTM D149	16 volts/micron (400 volts/mil)

HEALTH AND SAFETY

As long as normal good practice is observed **Thortex Flexi-Tech 60 F.G.** can be safely used.

Protective gloves should be worn.

A fully detailed **Material Safety Data Sheet** is either included with the material or is available on request.

PACKAGING

Supplied in 0.600 kg packs.

The information provided in this Product Data Sheet is intended as a general guide only and should not be used for specification purposes. The information is given in good faith but we assume no responsibility for the use made of the product or this information because this is outside the control of the company. Users should determine the suitability of the product for their own particular purposes by their own tests.



www.thortex.co.uk

Thortex Division of E. Wood Ltd.

Standard Way, Northallerton, N. Yorks. U.K. DL6 2XA

Tel: +44(0)1609 780170 Fax: +44(0)1609 780438 & 777905

E Mail: thortex@ewood.co.uk

Buy online: www.thortex.co.uk/shop