

**FLEX**  
by 3M™

INNOVATE. ILLUMINATE.

**3M**




## Take Light Wherever You Want To Go

Illuminated curves and straightaways come together in any combination you can imagine to create completely custom, beautifully luminous installations along walls, ceilings, or both. Mix and match six slender, lightweight, connectable components that use energy-efficient, replaceable LED sources combined with 3M technology to create an exceptionally even, luminous white glow.


Available in standard and custom finishes for even more flexibility. Whatever your design intent, FLEX enhances your creativity by letting you take light in an entirely new direction.

Just what you'd expect from 3M Architectural Markets, where state of the art meets high design.

### PRODUCT DETAILS



### STANDARD FINISHES



### FEATURES

- Uniformed luminance for a glare-free glow along the entire fixture.
- Quality LED modules are dimmable, low-maintenance, energy efficient and field replaceable.
- 0–10V dimming.
- Manufactured of a lightweight aluminum enclosure with slender profile of only 1.72" (4.37cm) thickness, allows for the creation of structures of almost any size or dimension.
- Suspension hardware for horizontal hanging or wall mounting included. Vertical and T-grid ceiling mounted suspension hardware kits are available for additional charge.
- Power supply kits and power cord included. Kit includes 96 Watt Power supply, 10 foot power cord and canopy hardware. Number of kits will depend on project's overall lighting layout. 3M will be happy to provide assistance in determining your project's needs.

Visit [3MArchitecturalMarkets.com/lighting](https://www.3M.com/ArchitecturalMarkets.com/lighting) to learn more.

